



# Signal Devices

## Visual 57/58mm Bracket Mount Beacons

### Features

- Choose from permanent incandescent, permanent LED, or flashing Xenon models
- Bracket mount installation
- 57 and 58mm diameters
- Light-intensive Xenon flash in flash models
- Bulb not included with incandescent models
- 2-year warranty



### Visual 57/58mm Bracket Mount Beacons 203, 204, and 205 Series Selection Chart

| Part Number                    | Price    | Color  | Drawing Link        | Description                                                      | Voltage                                                              | Current                                           | Starting Current | Operating Temp /Protection        | Life Duration     | Housing Material                    | Weight g [oz] | Connection                                                                                                    | Agency Approvals             |
|--------------------------------|----------|--------|---------------------|------------------------------------------------------------------|----------------------------------------------------------------------|---------------------------------------------------|------------------|-----------------------------------|-------------------|-------------------------------------|---------------|---------------------------------------------------------------------------------------------------------------|------------------------------|
| <b>25.8 mm (Bracket Mount)</b> |          |        |                     |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20310000</a>       | \$22.50  | Red    | <a href="#">PDF</a> | Incandescent Permanent Light 57mm                                | 12–240V AC/ DC max (depends on bulb selection; bulb sold separately) | Depends on bulb selection. (bulb sold separately) | -                |                                   | up to 5,000h      |                                     | 55 [1.94]     |                                                                                                               |                              |
| <a href="#">20320000</a>       | \$22.50  | Green  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20330000</a>       | \$22.50  | Yellow | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20340000</a>       | \$22.50  | Clear  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20350000</a>       | \$22.50  | Blue   | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20410067</a>       | \$89.00  | Red    | <a href="#">PDF</a> | LED Permanent Light 58mm                                         | 115VAC                                                               | < 25mA                                            | ≤ 0.5 A          | -4 to 122°F [-20 to 50°C]<br>IP65 | up to 100,000h    | Polycarbonate cap<br>Polyamide base | 72 [2.53]     | 2.5 mm² Screwless CAGE CLAMP® - technology (18–14 AWG)<br><br>Cable gland: m12 x1.5<br>Cable diameter: 3–6 mm | cULus file E164155, CE, RoHS |
| <a href="#">20420067</a>       | \$89.00  | Green  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20430067</a>       | \$89.00  | Yellow | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20440067</a>       | \$133.00 | Clear  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20450067</a>       | \$133.00 | Blue   | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20410075</a>       | \$73.00  | Red    | <a href="#">PDF</a> |                                                                  | 24V AC/DC                                                            | < 45mA                                            |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20420075</a>       | \$73.00  | Green  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20430075</a>       | \$73.00  | Yellow | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20440075</a>       | \$119.00 | Clear  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20450075</a>       | \$119.00 | Blue   | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20510055</a>       | \$106.00 | Red    | <a href="#">PDF</a> | Xenon Flashing Light (1Hz flash frequency, 1W flash energy) 58mm | 24VDC                                                                | < 100mA                                           | -                |                                   | 4,000,000 flashes |                                     | 88 [3.10]     |                                                                                                               |                              |
| <a href="#">20520055</a>       | \$110.00 | Green  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20530055</a>       | \$104.00 | Yellow | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20540055</a>       | \$110.00 | Clear  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20550055</a>       | \$110.00 | Blue   | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20510067</a>       | \$106.00 | Red    | <a href="#">PDF</a> |                                                                  | 115VAC                                                               | < 20mA                                            |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20520067</a>       | \$110.00 | Green  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20530067</a>       | \$104.00 | Yellow | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20540067</a>       | \$110.00 | Clear  | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |
| <a href="#">20550067</a>       | \$110.00 | Blue   | <a href="#">PDF</a> |                                                                  |                                                                      |                                                   |                  |                                   |                   |                                     |               |                                                                                                               |                              |

To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page.

## Bulbs



| Bulbs for Incandescent Permanent Visual Element |        |                                                  |         |         |               |
|-------------------------------------------------|--------|--------------------------------------------------|---------|---------|---------------|
| Part Number                                     | Price  | Description                                      | Wattage | Voltage | Life Duration |
| <a href="#">95584035</a>                        | \$8.75 | Bulb for Incandescent Light BA15d Bayonet Socket | 5W      | 24VDC   | up to 5,000h  |
| <a href="#">95584038</a>                        | \$8.75 |                                                  |         | 230VAC  |               |
| <a href="#">95584057</a>                        | \$8.75 |                                                  |         | 115VAC  |               |



# Signal Devices

## Beacon Accessories



| WERMA Beacons Accessories       |         |                     |                                                                                                                                             |                              |                                         |                     |
|---------------------------------|---------|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|-----------------------------------------|---------------------|
| Part Number                     | Price   | Drawing Link        | Description                                                                                                                                 | Operating Temp.              | Material                                | Weight              |
| Installation Beacon Accessories |         |                     |                                                                                                                                             |                              |                                         |                     |
| <a href="#">97581201</a>        | \$15.00 | <a href="#">PDF</a> | WERMA tube adapter, tube mount, 57mm diameter, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.              | -4 to 122°F<br>[-20 to 50°C] | Polyamide / Fiberglass                  | 1.13 g<br>[0.04 oz] |
| <a href="#">97581202</a>        | \$14.50 | <a href="#">PDF</a> | WERMA surface mounting base, base mount, black, polyamide. For use with beacons with 37mm (PG 29) mounting installation.                    |                              | Polyamide / Fiberglass with rubber seal | 2.83 g<br>[0.1 oz]  |
| <a href="#">97581503</a>        | \$46.00 | <a href="#">PDF</a> | WERMA beacon enclosure, surface mount, 1 hole. For use with beacons with 37mm (PG 29) mounting installation.                                |                              | Polycarbonate/<br>ABS blend             | 8.5 g<br>[0.3 oz]   |
| <a href="#">97581507</a>        | \$64.00 | <a href="#">PDF</a> | WERMA beacon enclosure, surface mount, 2 holes. For use with beacons with 37mm (PG 29) mounting installation.                               |                              |                                         | 14.17 g<br>[0.5 oz] |
| <a href="#">97581508</a>        | \$84.00 | <a href="#">PDF</a> | WERMA beacon enclosure, surface mount, 3 holes. For use with beacons with 37mm (PG 29) mounting installation.                               |                              |                                         | 17g<br>[0.6 oz]     |
| <a href="#">97581522</a>        | \$6.00  | <a href="#">PDF</a> | WERMA anti-twist washer, stainless steel. For use with Werma beacons with 37mm (PG 29) mounting installation.                               |                              | 304<br>Stainless steel                  | 0.57 g<br>[0.02 oz] |
| Freestanding Beacon Accessories |         |                     |                                                                                                                                             |                              |                                         |                     |
| <a href="#">96000001</a>        | \$18.00 | <a href="#">PDF</a> | WERMA mounting bracket, tube mount, black, polyamide. For use with 50mm or 70mm terminal elements. M16 x 1.5mm cable gland included.        | -4 to 122°F<br>[-20 to 50°C] | Polyamide                               | 57g<br>[2.01 oz]    |
| <a href="#">97520901</a>        | \$21.50 | <a href="#">PDF</a> | WERMA plastic base with integrated tube, base mount, 70mm diameter, 110mm length, black, polyamide. For use with 209 or 219 series beacons. |                              | Polyamide                               | 0.1 lbs<br>[1.6 oz] |
| <a href="#">97520902</a>        | \$6.00  | <a href="#">PDF</a> | WERMA cable gland, M25 x 1.5mm thread type, polyamide, black, accepts 8 to 17mm diameter cable, IP68.                                       |                              | Nylon                                   | 0.1 lbs<br>[1.6 oz] |
| <a href="#">97582603</a>        | \$45.00 | <a href="#">PDF</a> | WERMA galvanized wire guard, steel. For use with 826, 827, 828 or 829 series industrial signal beacons.                                     |                              | Wire D 3mm, chromed                     | 140g<br>[4.93 oz]   |
| <a href="#">97582605</a>        | \$10.50 | <a href="#">PDF</a> | WERMA mounting bracket, wall mount, black, ABS/ polycarbonate. For use with 826, 827, 828 and 829 series industrial signal beacons.         |                              | Polycarbonate/<br>ABS blend             | 62g<br>[2.19 oz]    |

