

wiha Screwdrivers

Tools that work for you

Insulated Screwdrivers

Wiha Insulated SoftFinish® Cushion Grip screwdrivers consist of Wiha engineered premium quality tool steel for strength and durability, have black oxide finish for corrosion protection, and feature exact fit precision machined tips for reduced cam-out. All Wiha insulated screwdrivers are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the jobsite, and CSA testing benchmarks for safety and performance. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.

**WT32091**

Features

- Ergonomic cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle directly molded to the blade for permanent bond
- Handle size proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Wiha premium quality tool steel for strength and durability
- Black oxide finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out
- Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind

Insulated Screwdrivers										
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Reduced Shank	Handle Length	Price
<u>WT32005</u>		 Slotted	2.0mm	0.4mm	6.5in (165mm)	2.4in (60mm)	0.20in (5.1mm)	No	4.1in (104mm)	\$6.25
<u>WT32010</u>			2.5mm		7.1in (180mm)	3.0in (75mm)	0.22in (5.6mm)			\$6.25
<u>WT32012</u>			3.0mm	0.6mm	8.0in (203mm)	3.9in (100mm)	0.27in (6.9mm)			\$6.25
<u>WT32015</u>			3.5mm							\$6.75
<u>WT32017</u>			4.0mm	0.8mm	8.3in (211mm)	4.9in (125mm)	0.29in (7.3mm)		4.4in (112mm)	\$8.00
<u>WT32024</u>			4.5mm	1.0mm	9.3in (236mm)		0.32in (8.1mm)			\$8.25
<u>WT32039</u>			6.5mm	1.2mm	10.6in (269mm)	5.9in (150mm)	0.38in (9.7mm)		4.7in (119mm)	\$11.25







Tools that work for you

Insulated Screwdrivers - Cont'd										
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Reduced Shank	Price
<u>WT32046</u>		 Slotted	3.5mm	0.6mm	8.0in (203mm)	3.9in (100mm)	0.14in (3.5mm)	4.1in (104mm)	Yes	\$12.25
<u>WT32049</u>			4mm	0.8mm	8.3in (211mm)		0.16in (4.0mm)	4.4in (112mm)		\$14.00
<u>WT32023</u>			4.5mm				0.24in (6.1mm)		No	\$7.75
<u>WT32052</u>					4.9in (125mm)	0.18in (4.6mm)	3.4in (86mm)	Yes	\$14.00	
<u>WT32055</u>			5.5mm	1.0mm		9.6in (243mm)	0.22in (5.6mm)	4.7in (119mm)	Yes	\$15.00
<u>WT32031</u>							0.28in (7.0mm)		No	\$8.50
<u>WT32026</u>					11.5in (292mm)	6.9in (175mm)	4.5in (114mm)	\$8.75		
<u>WT32034</u>			6mm	1.2mm	10.6in (269mm)	5.9in (150mm)	0.30in (7.6mm)	4.7in (119mm)		\$10.75
<u>WT32058</u>			6.5mm				0.26in (6.5mm)			Yes



Tools that work for you

Insulated Screwdrivers - Cont'd													
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Reduced Shank	Price				
WT32100		 Phillips	#0	6.5in (165mm)	2.4in (60mm)	0.25in (6.4mm)	4.1in (104mm)	No	\$6.75				
WT32101			#1	7.5in (191mm)	3.1in (80mm)	0.30in (7.6mm)	4.4in (112mm)		\$8.00				
WT32145				8.0in (203mm)		0.18in (4.6mm)	4.9in (124mm)	Yes	\$14.00				
WT32146			#2	8.3in (211mm)	3.9in (100mm)	0.24in (6.1mm)	4.4in (112mm)		\$17.00				
WT32102				8.6in (218mm)		0.35in (8.9mm)	4.7in (119mm)	No	\$9.75				
WT32103			#3	10.6in (269mm)	6.0in (150mm)	\$14.25							
WT32505		T5	6.5in (165mm)	2.4in (60mm)	0.45in (11.4mm)	4.1in (104mm)			\$7.00				
WT32531		T10			\$7.00								
WT32521		T8			0.18in (4.6mm)		\$6.75						
WT32526		T9			\$6.75								
WT32536		 Torx	T15	7.5in (191mm)	3.1in (80mm)	0.24in (6.1mm)	4.4in (112mm)		\$8.25				
WT32541			T20						\$8.50				
WT32546			T25	7.8in (198mm)	3.9in (100mm)	0.30in (7.6mm)	4.7in (119mm)		\$8.50				
WT32551			T27	8.6in (218mm)					\$10.50				
WT32556			T30						\$10.50				

Insulated Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Reduced Shank	Price
<u>WT30746</u>		 Plus-minus	#1	7.5in (191mm)	3.1in (80mm)	0.18in (4.6mm)	4.4in (112mm)	Yes	\$15.25
<u>WT30702</u>						0.24in (6.1mm)		No	\$8.50
<u>WT30747</u>			#2	8.6in (218mm)	3.9in (100mm)	0.24in (6.1mm)	4.7in (119mm)	Yes	\$19.00
<u>WT30704</u>						0.30in (7.6mm)		No	\$10.25
<u>WT35811</u>		 Square	#1	8.2in (210mm)	5.9in (150mm)	0.22in (5.6mm)	4.3in (109mm)	No	\$8.50
<u>WT35812</u>			#2	10.6in (269mm)		0.25in (6.4mm)	4.7in (119mm)		\$10.25

wiha Screwdrivers

Tools that work for you

Insulated Screwdriver Sets

Wiha Insulated SoftFinish® Cushion Grip screwdrivers consist of Wiha engineered premium quality tool steel for strength and durability, have black oxide finish for corrosion protection, and feature exact fit precision machined tips for reduced cam-out. All Wiha Insulated screwdrivers are VDE Certified and meet EN/IEC 60900 testing standards for protection against arc flash explosion, ASTM F1505 standard specifications for insulated and insulating hand tools, NFPA-70E standards for electrical safety on the jobsite, and CSA testing benchmarks for safety and performance. SoftFinish® driver handles feature an 8-edged large-diameter comfort grip for maximum gripping area, giving the user powerful torque and less fatigue.

Features

- Ergonomic cushion grip handle for comfort and control
- Dual durometer construction for long-lasting durability
- Handle directly molded to the blade for permanent bond
- Handle size proportionate to blade for consistent mechanical advantage
- Parallel flats for roll-off prevention
- Tip profile labeled on cap for easy identification
- Wiha premium quality tool steel for strength and durability
- Black oxide finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out
- Individually tested to 10,000 volts AC and rated to 1,000 volts AC for safety and peace of mind



WT32091

Insulated Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>WT32091</u>	5		 Phillips	#1 #2	(5) insulated SoftFinish screwdrivers (Phillips #1, #2, slotted 3.0mm, 4.5mm, 6.5mm)	\$42.25
			 Slotted	3.0mm 4.5mm 6.5mm		
<u>WT32099</u>	7		 Phillips	#1 #2 #3	(7) insulated SoftFinish screwdrivers (Phillips #1, #2, #3, slotted 3.0mm, 4.0mm, 5.5mm, 6.5mm)	\$63.25
			 Slotted	3.0mm 4.0mm 5.5mm 6.5mm		
<u>WT32059</u>	5		 Phillips	#1 #2	(5) insulated SoftFinish screwdrivers (Phillips: (#1, #2), slotted (4.5mm, 6.5mm), square: (#2))	\$39.50
			 Slotted	4.5mm 6.5mm		
			 Square	#2		
<u>WT32090</u>	4		 Phillips	#1 #2	(4) insulated SoftFinish screwdrivers (slotted: (3.5mm, 4.5mm), Phillips: (#1 #2))	\$31.00
			 Slotted	3.5mm 4.5mm		
<u>WT32092</u>	6		 Phillips	#1 #2 #3	(6) insulated SoftFinish screwdrivers (slotted: (3.5mm, 4.5mm, 6.5mm), Phillips: (#1, #2, #3))	\$55.00
			 Slotted	3.5mm 4.5mm 6.5mm		

Insulated Screwdriver Sets - Cont'd						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>WT32093</u>	10		⊕ Phillips #0 #1 #2 #3 ⊖ Slotted 2.0mm 2.5mm 3.0mm 3.5mm 4.5mm 6.5mm		(10) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.5mm, 6.5mm), Phillips: (#0, #1, #2, #3))	\$81.00
<u>WT32094</u>	13		⊕ Phillips #0 #1 #2 #3 ⊖ Slotted 2.0mm 2.5mm 3.0mm 3.5mm 4.5mm 5.5mm 6.5mm 8.0mm 10.0mm		(13) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.5mm, 5.5mm, 6.5mm, 8.0mm, 10.0mm), Phillips: (#0, #1, #2, #3))	\$120.00
<u>WT32097</u>	7		⊕ Phillips #1 #2 ⊖ Slotted 3.5mm 5.5mm 6.5mm ⊞ Square #1 #2		(7) insulated SoftFinish screwdrivers (slotted: (3.5mm, 5.5mm, 6.5mm), Phillips: (#1, #2), square: (#1, #2))	\$51.00
<u>WT32188</u>	7		⊕ Phillips #0 #1 ⊖ Slotted 2.0mm 2.5mm 3.0mm 3.5mm 4.0mm		(7) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm), Phillips: (#0, #1)), plastic molded case	\$59.00
<u>WT32190</u>	15		⊕ Phillips #1 #2 #3 ⊖ Slotted 2.0mm 2.5mm 3.0mm 3.5mm 4.5mm 6.5mm 8.0mm ⊞ Internal Hex 1/4in 5/16in 3/8in 7/16in 1/2in		(10) insulated SoftFinish screwdrivers (slotted: (2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.5mm, 6.5mm, 8.0mm), Phillips: (#1, #2, #3)), (5) insulated SoftFinish nut drivers (1/4in, 5/16in, 3/8in, 7/16in, 1/2in), fold out carry case	\$200.00
<u>WT32196</u>	6		⊕ Phillips #1 #2 ⊖ Slotted 4.5mm 6.5mm ⊞ Square #1 #2		(6) insulated SlimLine SoftFinish screwdrivers (slotted: (4.5mm, 6.5mm), Phillips: (#1, #2), square: (#1, #2))	\$56.00

Insulated Screwdriver Sets - Cont'd							
Part Number	Number of Pieces	Part Image	Type	Tip Size	Insulation Rating	Set Includes	Price
<u>WT32197</u>	8		⊕ Phillips #1 #2 ⊖ Slotted 3.5mm 4.0mm 4.5mm 5.5mm ⊞ Square #1 #2		1000V	(8) insulated SlimLine SoftFinish screwdrivers (slotted: (3.5mm, 4.0mm, 4.5mm, 5.5mm), Phillips: (#1, #2), square (#1, #2))	\$120.00
<u>WT32198</u>	11		⊕ Phillips #1 #2 ⊖ Slotted 3.5mm 4.0mm 4.5mm 5.5mm 6.5mm ⊞ Square #1 #2 ⊕⊖ Plus-minus #1 #2			(11) insulated SlimLine SoftFinish screwdrivers (slotted: (3.5mm, 4.0mm, 4.5mm, 5.5mm, 6.5mm), Phillips: (#1, #2), PlusMinus: (#1, #2), square: (#1, #2))	\$102.00
<u>WT32590</u>	6		⊗ Torx T8 T9 T10 T15 T20 T25			(6) insulated SoftFinish screwdrivers (torx: (T8, T9, T10, T15, T20, T25))	\$45.00
<u>WT35890</u>	6		⊕ Phillips #1 #2 ⊖ Slotted 4.5mm 6.5mm ⊞ Square #1 #2			(6) insulated SoftFinish screwdrivers (slotted: (4.5mm, 6.5mm), Phillips: (#1, #2), square: (#1, #2))	\$54.00