

wiha Screwdrivers

Tools that work for you

Precision Screwdrivers

Wiha Precision Screwdrivers feature cushion-grip handles for comfort and control, and the dual durometer material is direct molded to the blade for a permanent bond. The Precision style includes a hex profile finger grip for precise torque and a tapered handle for rapid rotation. The handles are sized proportionate to the tip and feature an extra-long handle with a smooth-turning cap for multiple hand positions. The driver tip profiles are labeled on the handle to quickly and easily identify the driver.



Features

- Handle direct molded to blade for a permanent bond
- Tapered handle for rapid rotation
- Extra-long handle for optimal hand positions and smooth turning
- Tip profile labeled on handle for easy identification
- Handle sized proportionate to the blade for consistent mechanical advantage
- Wiha engineered premium quality tool steel for strength and durability
- Chrome-plated satin finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out

Precision Screwdrivers											
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price	
<u>WT26008</u>		 Slotted	0.8mm	0.16mm	4.7in (119mm)	1.6in (40mm)	0.08in (2.0mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$7.00	
<u>WT26010</u>			1.0mm	0.18mm						\$6.50	
<u>WT26012</u>			1.2mm	0.2mm						\$5.50	
<u>WT26015</u>			1.5mm	0.25mm						\$5.00	
<u>WT26018</u>			1.8mm	0.3mm						\$5.00	
<u>WT26020</u>			2.0mm	0.4mm	5.7in (145mm)	2.0in (50mm)		3.7in (94mm)		\$4.75	
<u>WT26022</u>										\$4.75	
<u>WT26023</u>										\$4.75	

wiha Screwdrivers

Tools that work for you

Precision Screwdrivers - Cont'd										
Part Number	Part Image	Type	Tip Size	Slotted Tip Thickness	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>WT26025</u>		 Slotted	2.5mm	0.4mm	5.7in (145mm)	2.0in (50mm)	0.10in (2.5mm)	3.7in (94mm)	Cushion grip handle with rotating cap	\$4.50
<u>WT26027</u>					7.7in (196mm)	3.9in (100mm)		3.8in (97mm)		\$4.50
<u>WT26028</u>					9.6in (243mm)	5.9in (150mm)		3.7in (94mm)		\$5.50
<u>WT26030</u>			3.0mm	0.5mm	5.7in (145mm)	2.0in (50mm)	0.12in (3.0mm)			\$4.25
<u>WT26032</u>					6.7in (170mm)	2.4in (60mm)		4.3in (109mm)		\$4.50
<u>WT26033</u>					8.3in (211mm)	3.9in (100mm)		4.4in (112mm)		\$5.00
<u>WT26034</u>					10.2in (259mm)	5.9in (150mm)		4.3in (109mm)		\$5.75
<u>WT26035</u>			3.5mm	0.6mm	6.7in (170mm)	2.4in (60mm)	0.14in (3.5mm)			\$4.75
<u>WT26040</u>			4.0mm	0.8mm	8.3in (211mm)	3.9in (100mm)	0.16in (4.0mm)	4.4in (112mm)		\$5.25
<u>WT26041</u>										\$5.00
<u>WT26042</u>										10.2in (259mm)
<u>WT26074</u>			3.5mm	0.6mm	6.3in (160mm)	2.4in (60mm)	0.14in (3.5mm)	3.9in (99mm)		\$6.25



Tools that work for you

Precision Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>WT26102</u>		⊕ Phillips	#000	4.7in (119mm)	1.6in (40mm)	0.08in (2.0mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$6.75
<u>WT26100</u>			#00						\$5.25
<u>WT26105</u>			#0	5.7in (145mm)	2.0in (50mm)	0.12in (3.0mm)	3.7in (94mm)		\$4.75
<u>WT26108</u>				6.7in (170mm)	3.0in (75mm)				\$4.50
<u>WT26109</u>				9.6in (243mm)	5.9in (150mm)				\$6.00
<u>WT26110</u>			#1	6.7in (170mm)	2.4in (60mm)	0.16in (4.0mm)	4.3in (109mm)		\$5.00
<u>WT26115</u>				10.2in (259mm)	5.9in (150mm)				\$6.25



Tools that work for you

Precision Screwdrivers - Cont'd									
Part Number	Part Image	Type	Tip Size	Overall Length	Shaft Length	Shaft Diameter	Handle Length	Handle Type	Price
<u>WT26307</u>		 External Hex	0.7mm (.028in)	4.7in (119mm)	1.6in (40mm)	0.10in (2.5mm)	3.1in (79mm)	Cushion grip handle with rotating cap	\$5.00
<u>WT26309</u>			0.9mm (.035in)						\$5.00
<u>WT26313</u>			1.3mm (.050in)						\$4.75
<u>WT26315</u>			1.5mm	5.7in (145mm)	2.0in (50mm)	0.09in (2.3mm)	3.7in (94mm)		\$4.75
<u>WT26316</u>			1/16in						\$4.25
<u>WT26320</u>			2.0mm (5/64in)						\$4.25
<u>WT26323</u>			3/32in	6.7in (170mm)	2.4in (60mm)	0.11in (2.9mm)	4.3in (109mm)		\$4.00
<u>WT26325</u>			2.5mm						\$4.25
<u>WT26326</u>			7/64in			0.12in (3.0mm)			\$3.75
<u>WT26334</u>			3mm			0.14in (3.5mm)			\$3.75
<u>WT26335</u>			1/8in			0.15in (3.8mm)			\$3.75

wiha Screwdrivers

Tools that work for you

Precision Screwdriver Sets

Wiha Precision Screwdrivers feature cushion-grip handles for comfort and control, and the dual durometer material is direct-molded to the blade for a permanent bond. The precision style includes a hex profile finger grip for precise torque and a tapered handle for rapid rotation. The handles are sized proportionate to the tip and feature an extra-long handle with a smooth-turning cap for multiple hand positions.

Features

- Handle direct molded to blade for a permanent bond
- Tapered handle for rapid rotation
- Extra-long handle for optimal hand positions and smooth turning
- Tip profile labeled on handle for easy identification
- Handle sized proportionate to the blade for consistent mechanical advantage
- Wiha engineered premium quality tool steel for strength and durability
- Chrome-plated satin finish for corrosion protection
- Exact fit precision machined tip for reduced cam-out



Precision Screwdriver Sets						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>WT26090</u>	6		 Slotted	1.5mm 2mm 2.5mm 3mm 3.5mm 4mm	(6) precision screwdrivers (slotted: (1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm))	\$27.00
<u>WT26092</u>	7		 Phillips	#0	(7) precision screwdrivers (slotted: (2.5 x 50mm, 2.5, 3.0, 4.0 x 100mm, 3.0, 4.0 x 150mm), Phillips (#0 x 75mm))	\$33.00
			 Slotted	2.5mm 3mm 4mm		
<u>WT26098</u>	8		 Slotted	1mm 1.2mm 1.5mm 2mm 2.5mm 3mm 3.5mm 4mm	(8) precision screwdrivers (slotted: (1.0mm, 1.2mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm, 3.5mm, 4.0mm)), canvas pouch.	\$42.00
<u>WT26192</u>	5		 Phillips	#0 #1	(5) precision screwdrivers (slotted: (2.5mm, 3.0mm, 4.0mm), Phillips: (#0, #1))	\$30.00
			 Slotted	2.5mm 3.0mm 4.0mm		
<u>WT26194</u>	4		 Phillips	#000 #00 #0 #1	(4) precision screwdrivers (Phillips: (#000, #00, #0, #1))	\$20.00
<u>WT26197</u>	7		 Phillips	#00 #0 #1	(7) precision screwdrivers (Phillips: (#00, #0, #1), slotted (1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$31.00
			 Slotted	1.5mm 2.0mm 2.5mm 3.0mm		
<u>WT26199</u>	8		 Phillips	#000 #00 #0 #1	(8) precision screwdrivers (slotted: (1.0mm, 2.0mm, 3.0mm, 4.0mm), Phillips: (#000, #00, #0, #1)), canvas pouch	\$45.00
			 Slotted	1.0mm 2.0mm 3.0mm 4.0mm		

Precision Screwdriver - Cont'd						
Part Number	Number of Pieces	Part Image	Type	Tip Size	Set Includes	Price
<u>WT26390</u>	7		External Hex	0.7mm 0.9mm 1.3mm 1.5mm 2mm 2.5mm 3mm	(7) precision screwdrivers (hex: (0.7mm, 0.9mm, 1.3mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$31.00
<u>WT26391</u>	8			0.028in 0.035in 0.050in 1/16in 5/64in 3/32in 7/64in 1/8in	(8) precision screwdrivers (hex: (0.028in, 0.035in, 0.050in, 1/16in, 5/64in, 3/32in, 7/64in, 1/8in))	\$35.00
<u>WT26491</u>	5		Ball-end Hex	1.35mm 1.5mm 2mm 2.5mm 3mm	(5) precision screwdrivers (ball end hex: (1.35mm, 1.5mm, 2.0mm, 2.5mm, 3.0mm))	\$26.00
<u>WT26791</u>	8		Torx	T1 T2 T3 T4 T5 T6 T7 T8	(8) precision screwdrivers (torx: (T1, T2, T3, T4, T5, T6, T7, T8))	\$48.00
<u>WT26799</u>	8			T3 T4 T5 T6 T7 T8 T9 T10	(8) precision screwdrivers (torx: (T3, T4, T5, T6, T7, T8, T9, T10)), roll up pouch	\$54.00