



TOSHIBA SD SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED & HAZARDOUS LOC, 10HP, 3-PH, 230/460 VAC, 1200RPM, TEFC, 256T FRAME, CAST IRON, RIGID BASE ONLY MOUNT

0106SDSR41A-P

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
6/19/2023

SHEET 1 OF 1