



ISOMETRIC VIEW

STEGO SMART SENSOR TEMPERATURE/HUMIDITY SENSOR, -40 TO 140 DEG F, 0 TO 100% RH, IO-LINK OUTPUT,  
35MM DIN RAIL OR PANEL MOUNT, M12 AXIAL MALE A-CODED 4-PIN.

014112-00

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
[mm]

LATEST VERSION  
7/28/2022

SHEET 1 OF 1