



ISOMETRIC VIEW

STEGO EXHAUST FAN, TOP MOUNT, 203 CFM, 24 VDC OPERATING VOLTAGE, G3 (COARSE) FILTER MAT, NEMA 3R, INDOOR USE ONLY, 9.69 X 9.69IN ENCLOSURE CUTOUT, RAL 7035 LIGHT GRAY.

018600-04

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
7/28/2022

SHEET 1 OF 1