


DETAIL A  
SCALE 2:1



WEG ELECTRIC S PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED & HAZARDOUS LOC, 20HP, 3-PH, 208-230/460 VAC, 1800RPM, TEFC, 256TC FRAME, ROLLED STEEL, C-FACE /RIGID BASE MOUNT

02018ET3E256TC-S

AutomationDirect.com  
1-800-633-0405



### 3rd ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
2/14/2024

SHEET 1 OF 1