



TOSHIBA SD SERIES PREMIUM EFFICIENCY AC INDUCTION MOTOR, GENERAL PURPOSE, INVERTER RATED & HAZARDOUS LOC, 20HP, 3-PH, 230/460 VAC, 1800RPM, TEFC, 256T FRAME, CAST IRON, RIGID BASE ONLY MOUNT

0204SDSR41A-P

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
6/22/2023

SHEET 1 OF 1