



ISOMETRIC VIEW

STEGO ENCLOSURE HEATER, 100W HEATING CAPACITY, TOUCH-SAFE PTC RESISTOR HEATING ELEMENT, 120-240 VAC/VDC OPERATING VOLTAGE, 50/60 HZ, FIXED THERMOSTAT, N.C. (OPEN ON RISE) 41 DEG F (5 DEG C) SWITCH-ON, 35MM DIN RAIL OR PANEL MOUNT.

06513.0-00

AutomationDirect.com  
1-800-633-0405

<p>3rd ANGLE</p>	<p>NOT TO SCALE</p>	<p>PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES</p>	<p>METRIC UNITS USED FOR PART DESIGN</p>	<p>UNLESS OTHERWISE SPECIFIED UNITS ARE: <b>inch [mm]</b></p>	<p>LATEST VERSION 2/13/2024</p>	<p>SHEET 1 OF 1</p>
------------------	---------------------	----------------------------------------------------------------------------	------------------------------------------	---------------------------------------------------------------	-------------------------------------	---------------------