



ISOMETRIC VIEW

STEGO ENCLOSURE HEATER, 150W HEATING CAPACITY, TOUCH-SAFE PTC RESISTOR HEATING ELEMENT, 120-240 VAC/VDC OPERATING VOLTAGE, 50/60 HZ, FIXED THERMOSTAT, N.C. (OPEN ON RISE) 41 DEG F (5 DEG C) SWITCH-ON, 35MM DIN RAIL OR PANEL MOUNT.

06514.0-00

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
2/13/2024

SHEET 1 OF 1