



ISOMETRIC VIEW

JAM NUT

4-CONDUCTOR SHIELDED CABLE,  
1 METER LONG

M5 X 0.8 THREAD  
(10-32 UNF OPTIONAL)

STEGO EXHAUST VENT, TOP MOUNT, G3 (COARSE) FILTER MAT, NEMA 3R, 9.69 X 9.69IN ENCLOSURE CUTOUT,  
RAL 7035 LIGHT GRAY.

**118600-00**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
7/28/2022

SHEET 1 OF 1