


ISOMETRIC VIEW



STEGO ENCLOSURE HEATER, AXIAL FAN, 200W HEATING CAPACITY, HIGH PERFORMANCE CARTRIDGE HEATING ELEMENT, 24 VDC  
OPERATING VOLTAGE, ADJUSTABLE THERMOSTAT, N.C. (OPEN ON RISE) -4 TO 104 DEG F, 35MM DIN RAIL OR PANEL MOUNT.

130921-16

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
7/28/2022

SHEET 1 OF 1