


POLYCARBONATE
VERSION ONLY
c  US LISTED
FILE #E65324
TYPE 4,4X,6,6P

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE


Purchased assembly includes styled box, flanged lid, 4 cover screws, and preformed silicone gasket.

General Purpose ABS version is not UL approved. (Matl UL94 - HB)

Polycarbonate version is UL 508 approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 2.5 lbf-in (30 cN-m)

| 1555QF | |
|---|-------------|
| 1555QF Regular Enclosure | |
| General Purpose ABS RAL-7035 | 1555QF17GY |
| Polycarbonate RAL-7035 | 1555Q2F17GY |
| ACCESSORIES | |
| Steel Inner Panels | 1554QPL |
| Silicone Pre-formed Gasket Black (Pkg 2) | 1554QGASKET |
| Steel Panel / P.C. Board Self Tapping Screw [#4 X 1/4" (6.4mm) Plated] | 1555TS100 |
| Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50) | SC576-50 |



HAMMOND
MANUFACTURING®

1555QF17

www.hammondmfg.com

Dimensions:
mm
[inches]