


ISOMETRIC VIEW



STEGO ENCLOSURE HEATER, 20W HEATING CAPACITY, PTC RESISTOR HEATING ELEMENT, 120-240 VAC/VDC  
OPERATING VOLTAGE, 50/60 HZ, 35MM DIN RAIL OR PANEL MOUNT.

16401.9-00

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
2/13/2024

SHEET 1 OF 1