


ISOMETRIC VIEW



STEGO ENCLOSURE HEATER, 40W HEATING CAPACITY, PTC RESISTOR HEATING ELEMENT, 120-240 VAC/VDC
OPERATING VOLTAGE, 50/60 HZ, 35MM DIN RAIL OR PANEL MOUNT.

16403.9-00

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
2/13/2024

SHEET 1 OF 1