



2-WAY, 2-POSITION, N.C., LOW LEAD BRASS BODY, 3/8IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), CV=4.5, 180 PSI MAXIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18IN PIGTAIL.

SPARTAIN SOLENOID VALVE

3516-6Q001-BAC7B-A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
2/6/2023

SHEET 1 OF 1