



2-WAY, 2-POSITION, N.C., LOW LEAD BRASS BODY, 1/2IN FEMALE NPT INLET(s), 1/2IN FEMALE NPT OUTLET(s), CV=4.5, 180 PSI MAXIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18IN PIGTAIL.

## SPARTAN SOLENOID VALVE

3516-6Q001-BAD7B-A

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
2/6/2023

SHEET 1 OF 1