



2-POSITION, N.C., GLASS-FILLED NYLON BODY, 1/8IN FEMALE NPT INLET(s), 1/8IN FEMALE NPT OUTLET(s), CV=0.24, 200 PSI MAXIMUM OPERATING PRESSURE, 24 VDC OPERATING VOLTAGE, 18IN PIGTAIL.

**SPARTAN SOLENOID VALVE**

**3827-670-AA83B-A**

AutomationDirect.com  
 1-800-633-0405



3rd ANGLE

NOT TO SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR PART DESIGN

UNLESS OTHERWISE SPECIFIED UNITS ARE:

**inch**  
**[mm]**

LATEST VERSION  
 2/6/2023

SHEET 1 OF 1