



Ø0.88
[22.2]



2.53
[64.1]


1.16
[29.5]



0.90
[22.8]

1.81
[46.1]


#8-32
THREAD
X2



0.87
[22.0]

0.87
[22.0]

3/8" NPT
PORT X2




1.47
[37.4]

3.88
[98.5]

3.21
[81.5]

1.20
[30.6]

0.46
[11.7]



2-WAY, 2-POSITION, N.C., GLASS-FILLED NYLON BODY, 3/8IN FEMALE NPT INLET(S), 3/8IN FEMALE NPT OUTLET(S), CV=0.72, 40 PSI MAXIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

SPARTAN SOLENOID VALVE

6200-680-AAC7C-A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
1/26/2023

SHEET 1 OF 1