



2-WAY, 2-POSITION, N.C., LOW LEAD BRASS BODY, 3/8IN FEMALE NPT INLET(s), 3/8IN FEMALE NPT OUTLET(s), CV=0.52, 125 PSI MAXIMUM OPERATING PRESSURE, 120 VAC OPERATING VOLTAGE, 18mm DIN STYLE WIRING PLUG.

**SPARTAN SOLENOID VALVE**

**6222-6K001-AAC7C-A**

AutomationDirect.com  
1-800-633-0405

 3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>inch</b> <b>[mm]</b>	LATEST VERSION 1/26/2023	SHEET 1 OF 1
--	--------------	---	---------------------------------	---------------------------------------	----------------------------	-----------------------------	--------------