


ISOMETRIC VIEW



DETAIL A
SCALE 1.5 : 1
(4X)

ACHIEVE IEC LIMIT SWITCH, ONE-WAY HORIZONTAL LEVER WITH METAL ROLLER AND DUST CAP, 90-DEGREE ADJUSTABLE HEAD, (1) N.O./ (1) N.C. CONTACT(S), SNAP ACTION, 20-22MM OR 40-42MM HOLE SPACING, PLASTIC, (2) PG11 CABLE ENTRIES WITH (1) 1/2IN NPT ADAPTER.

ADP2T35Z11

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/16/2023

SHEET 1 OF 1