



ISOMETRIC VIEW

ACHIEVE COMPACT LIMIT SWITCH, SIDE ROTARY ADJUSTABLE LEVER WITH 18MM NYLON ROLLER, (2) N.O./(2) N.C. CONTACT(S), SNAP ACTION, 25MM HOLE SPACING, ZINC ALLOY, PIGTAIL, 9.8FT/3M CABLE LENGTH, BOTTOM EXIT.

AEM2G5120Z22-3

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/17/2023

SHEET 1 OF 1