


THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2023 ROBROY ENCLOSURES

- ASSEMBLY:**
- 1: (1) ACCESSORY KIT (WPPCACCKITNOFT) SHALL BE PACKAGED LOOSELY INSIDE ENCLOSURE
 - 2: (1) STYROFOAM SHEET SHALL BE PLACED ON TOP OF COVER INSIDE CARTON

SPECIAL REQUIREMENTS

NEMA 250: TYPE 1, 3R, 4, 4X, 6P, 12 IEC 60529: IP66, IP68			STANDARD P/N: AH14124CSS		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03		.XXX ± 0.010	
COLOR: N/A COLOR STANDARD: PANTONE 7541 C			CUSTOMER DWG:		<div><div> AttaBox</div><div>A ROBROY ENCLOSURES™ BRAND</div></div> <div><div>Robroy Enclosures</div><div>500 Maple Street</div><div>Belding, Michigan 48809</div><div>Phone: 616-794-0700</div><div>Fax: 616-749-3378</div></div> <div>DWG AH14124CSS</div>							
MATERIAL: POLYCARBONATE												
REVISION HISTORY												
REV	DESCRIPTION		DATE	ENG	DRAWN BY BH		DATE 11/10/23		CUSTOMER		DWG AH14124CSS	
-	-		-	-	-		-		-		-	
-	-		-	-	-		-		-		-	
-	-		-	-	-		-		-		-	
-	-		-	-	-		-		-		-	
-	-		-	-	-		-		-		-	
-	-		-	-	-		-		-		-	
-	-		-	-	-		-		-		-	
SCALE					DO NOT SCALE		DESCRIPTION STANDARD ENCLOSURE		PART NUMBER AH14124CSS			



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378