


ISOMETRIC VIEW



DETAIL A
SCALE 2 : 1.5
(2X)

ACHIEVE IEC LIMIT SWITCH, METAL PLUNGER, 90-DEGREE ADJUSTABLE HEAD, (2) N.C. CONTACT(S), SNAP ACTION, WITH RESET, 20-22MM HOLE SPACING, PLASTIC, (2) PG11 AND (1) 1/2IN NPT CABLE ENTRIES.

AHP2T11J02-024

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/17/2023

SHEET 1 OF 1