



Motor Connector



SECTION A-A'

SIGNAL	PIN No.	WIRE COLOR
U	A	Red
V	B	White
W	C	Blue
FG	D	Grn/Yel
BK+	E	White
BK-	F	Black
N/C	G	N/C

CABLE PART#	LENGTH 'L'(m)	LENGTH 'L'(ft)
APCS-PN03NB-AD	3m	9.8ft
APCS-PN05NB-AD	5m	16.4ft
APCS-PN10NB-AD	10m	32.8ft
APCS-PN20NB-AD	20m	65.6ft
APCS-PF03NB-AD	3m	9.8ft
APCS-PF05NB-AD	5m	16.4ft
APCS-PF10NB-AD	10m	32.8ft
APCS-PF20NB-AD	20m	65.6ft

LS ELECTRIC POWER CABLE, MATING CONNECTORS, 32.8ft/10m CABLE LENGTH, FOR USE WITH 230 VAC APM-FE MOTORS WITH BRAKE

APCS-PN10NB-AD

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/9/2022

SHEET 1 OF 1