



Motor Connector



SECTION A-A'

| SIGNAL | PIN No. | WIRE COLOR |
|--------|---------|------------|
| U | A | Red |
| V | B | White |
| W | C | Blue |
| FG | D | Grn/Yel |

| CABLE PART# | LENGTH 'L'(m) | LENGTH 'L'(ft) |
|----------------|---------------|----------------|
| APCS-PN03IS-AD | 3m | 9.8ft |
| APCS-PN05IS-AD | 5m | 16.4ft |
| APCS-PN10IS-AD | 10m | 32.8ft |
| APCS-PN20IS-AD | 20m | 65.6ft |
| APCS-PF03IS-AD | 3m | 9.8ft |
| APCS-PF05IS-AD | 5m | 16.4ft |
| APCS-PF10IS-AD | 10m | 32.8ft |
| APCS-PF20IS-AD | 20m | 65.6ft |

LS ELECTRIC POWER CABLE, MATING CONNECTORS, 65.6ft/20m CABLE LENGTH, FOR USE WITH 230 VAC APM-FF35D
MOTORS WITHOUT BRAKE

APCS-PN20IS-AD

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/9/2022

SHEET 1 OF 1