




TECHNICAL INFORMATION

- 1.) SENSING SURFACE
- 2.) HOUSING
- 3.) COVER
- 4.) POWER INDICATOR GREEN
- 5.) FUNCTION INDICATOR YELLOW

ISOMETRIC VIEW (ASSEMBLED)



BALLUFF CAPACITIVE PROXIMITY SENSOR, RECTANGULAR, 34 X 16 X 8MM BODY, POLYPROPYLENE (PP) HOUSING, TOP SENSING, PNP, N.O., 8MM SENSING DISTANCE, FLUSH, 100 HZ SWITCHING FREQUENCY, IP67, 4-PIN M12 QUICK-DISCONNECT.

BCS012T

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
7/25/2023

SHEET 1 OF 1