


**CLAMPING RANGE Ø4.0 - 8.0MM [0.16 - .031]**  
**SHIELDING DIAMETER 2.5 - 6.0 [0.10 - 0.24]**

7	1	O-RING Ø12x1.5	NBR
6	1	PG 9 GLANDS CAP (4.VERSION)	Brass (nickel plated)
5	1	PG 9 SEAL	CR
4	1	PG 9 PLASTIC INSERT (4. VERSION)	PA 6
3	1	PG 9/M16 EMC PRESSURE RING	Brass (nickel plated)
2	1	PG 9/M16 EMC SPRING	CuBe (tin plated)
1	1	PG 9/PG 9 EMC CABLE GLAND BODY (TL6)	Brass (nickel plated)
No/Nu.	Qty/Ad.	Part Name/Parça Adı	Material/Malzeme
Part List / Parça Listesi			

	-	-	-	-	-	-
Revision Revizyon	No Nu.	Item No Unsur Nu.	Date Tarih	Request No Talep No	Realised By Gerçekleştiren	Approved By Onaylayan

Drawing Number / Resim No	2870	PG 9 EMC CABLE GLAND EURO (PG9) TL6				
1st Discl.Request #/Y.Yn.Tal.No	15-089	PG 9 EMC RAKOR EURO (PG9) TL6				
Bimed Code / Bimed Kodu	BSEM-E2 (PG9T)	Date / Tarih	Signature / İmza	Material / Malzeme	Mass / Ağırlık	32,866 g
Reference Number / Ref. No	-	16.02.2015				
Designed by / Tasarlayan	Nursel ORAL					
Drawn by / Çizen	Nursel ORAL					
Approved by / Onaylayan	Yılmaz ALBUKREK					
Scale / Ölçek	Form					
4/1	A3					