



**CLAMPING RANGE Ø6.0 - 12.0 [0.24 - 0.47]**  
**SHIELDING DIAMETER 4.5 - 10.0 [0.18 - 0.39]**

7	1	Ø16x1.5 O-RING	NBR
4	1	PG 13.5 PLASTIC INSERT (4.VERSION)	PA6 V2
5	1	PG 13.5 RUBBER SEALING	CR
2	1	PG 13.5/M20 EMC SPRING	CuBe (Tin Plated)
6	1	PG 13.5 GLANDS CAP (4.VERSION)	Brass (Nickel Plated)
3	1	PG 13.5/M20 EMC PRESSURE RING	Brass (Nickel Plated)
1	1	PG 13.5/PG 13.5 EMC GLAND BODY (TL6.5)	Brass (Nickel Plated)
No/Nu.	Qty/Ad.	Part Name/Parça Adı	Material/Malzeme
Part List / Parça Listesi			

	-	-	-	-	-	-
Revision Revizyon	No Nu.	Item No Unsur Nu.	Date Tarih	Request No Talep No	Realised By Gerçekleştiren	Approved By Onaylayan

Drawing Number / Resim No	-	PG 13.5 EMC RAKOR (PG13.5) TL6.5				
1st Discl.Request #/Y.Yn.Tal.No	-	PG 13.5 EMC CABLE GLAND (PG13.5) TL6.5				
Bimed Code / Bimed Kodu	BSEM-E4 (PG13.5T)	Date / Tarih	Signature / İmza	Material / Malzeme	Mass / Ağırlık	41,246 g
Reference Number / Ref. No	-	22.04.2014				
Designed by / Tasarlayan	Nursel ORAL					
Drawn by / Çizen	Nursel ORAL					
Approved by / Onaylayan	Yılmaz ALBUKREK					
Scale / Ölçek	Form	bimed				
-	A3					