


Color and Length Part Number Combinations

C6A-STPnn-Sxx

nn	Color	Sxx	Length
BK	Black	S3	3FT
BL	Blue	S7	7FT
GN	Green	S10	10FT
GY	Grey	S14	14FT
OR	Orange	S25	25FT
PL	Purple	S50	50FT
YL	Yellow		
RD	Red		

Notes:

1. CABLE - UL Type CM, 26AWG*4P + AEB, OD: 6.0MM, Rated 75°C
2. RJ45 8P8C Shielded Plug
3. Minimum Bending Radius: 48MM [1.88"]
4. Operating Temperature: 0-60°C [32-140°F]

C6A-STPnn-Sxx	
Rev: original	Date: 9/15/2022
Units: mm [inches]	
Scale: 1:1	
Cat 6A Ethernet Patch Cable	
 AUTOMATIONDIRECT .com	