

Technical drawing of the M3.5 terminal screw assembly, showing dimensions in mm and inches.

Front View (Left):

- MOUNTING HOLE: 3.2 [0.13]
- R0.8 [R0.03]
- 24.1 [0.95]
- Ø22.3 [Ø0.88]

Side View (Middle):

- M3.5 TERMINAL SCREW
- 1.0 [0.04]
- 50.5 [1.99]
- 18.5 [0.73]
- 24.0 [0.94]
- 30.0 [1.18]
- 1.0 [0.04] PANEL THICKNESS
- PACKING (NUMBER OF PACKINGS REDUCED WITH ATTACHMENT PLATE THICKNESS)

Top View (Right):

- 30.0 [1.18]
- 37.0 [1.46]


1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

DR22B8-EB

Units: mm [inch]

Full Scale

BUZZER 22mm, ELEC SOUND, 80dB at 10CM,
12-24V, INTERMITTENT/CONTINUOUS SOUND
SELECTION, IP54

 AUTOMATIONDIRECT.com