


CONTRINEX INDUCTIVE PROXIMITY SENSOR, TUBULAR, 30MM DIAMETER X 63.5MM BODY, 304 STAINLESS STEEL HOUSING, PNP, N.O., 12MM SENSING DISTANCE, NON-FLUSH, 90 HZ SWITCHING FREQUENCY, IP68 IP69K, 4-PIN M12 QUICK-DISCONNECT.					DW-AS-713-M30-967			AutomationDirect.com 1-800-633-0405	
	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 9/27/2022	SHEET 1 OF 1	