


ISOMETRIC VIEW



CONTRINEX INDUCTIVE PROXIMITY SENSOR, TUBULAR, 12MM DIAMETER X 61MM BODY, 304 STAINLESS STEEL HOUSING, PNP, N.O., 1.5MM SENSING DISTANCE, FLUSH, 850 HZ SWITCHING FREQUENCY, IP68 IP69K, 4-PIN M12 QUICK-DISCONNECT.

**DW-LS-703-P12G**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
9/27/2022

SHEET 1 OF 1