






DETAIL A
SCALE 2 : 1
MALE 4-WIRE
4-POLE



DETAIL B
SCALE 2 : 1
FEMALE 4-WIRE
4-POLE



M8 AXIAL MALE TO RIGHT-ANGLE FEMALE, 4-POLE, PVC JACKET, ORANGE, 1.9FT/0.6M CABLE LENGTH, IP65, IP67, IP68 AND IP69K, SUITABLE FOR FOOD AND BEVERAGE APPLICATIONS.

AUTOMATIONDIRECT CONNECTION CABLE

EVT433

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
12/6/2023

SHEET 1 OF 1