






DETAIL A  
SCALE 2 : 1  
MALE 4-WIRE  
4-POLE



DETAIL B  
SCALE 2 : 1  
FEMALE 4-WIRE  
4-POLE



M8 AXIAL MALE TO RIGHT-ANGLE FEMALE, 4-POLE, PVC JACKET, ORANGE, 3.2FT/1M CABLE LENGTH, IP65, IP67, IP68 AND IP69K, SUITABLE FOR FOOD AND BEVERAGE APPLICATIONS.

# AUTOMATIONDIRECT CONNECTION CABLE

EVT434

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
12/6/2023

SHEET 1 OF 1