


ISOMETRIC VIEW



AXIAL VERSION

PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, DIFFUSE, INFRARED LIGHT EMISSION, 100MM SENSING DISTANCE, SELECTABLE LIGHT-ON/DARK-ON, NPN, 500 HZ SWITCHING FREQUENCY, POLYBUTYLENE TEREPHTHALATE HOUSING, PIGTAIL.

**F18I2-0N-0A**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
2/24/2023

SHEET 1 OF 1