


AXIAL VERSION



ISOMETRIC VIEW

PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, DIFFUSE, INFRARED LIGHT EMISSION, 700MM SENSING DISTANCE, SELECTABLE LIGHT-ON/DARK-ON, NPN, POTENTIOMETER, 500 HZ SWITCHING FREQUENCY, POLYBUTYLENE TEREPHTHALATE HOUSING, PIGTAIL.

**F18I6-0N-0A**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
2/28/2023

SHEET 1 OF 1