



ISOMETRIC VIEW

AXIAL VERSION

PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, DIFFUSE, INFRARED LIGHT EMISSION, 700MM SENSING DISTANCE, COMPLEMENTARY LIGHT-ON/DARK-ON, NPN, POTENTIOMETER, 1000 HZ SWITCHING FREQUENCY, POLYBUTYLENE TEREPHTHALATE HOUSING, PIGTAIL.

F18I8-BN-0A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/28/2023

SHEET 1 OF 1