



ISOMETRIC VIEW

PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, DIFFUSE, INFRARED LIGHT EMISSION, 700MM SENSING DISTANCE, COMPLEMENTARY LIGHT-ON/DARK-ON, PNP, POTENTIOMETER, 1000 HZ SWITCHING FREQUENCY, POLYBUTYLENE TEREPHTHALATE HOUSING, PIGTAIL.

F18I8-BP-0A

AutomationDirect.com
1-800-633-0405

<p>3rd ANGLE</p>	<p>NOT TO SCALE</p>	<p>PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES</p>	<p>METRIC UNITS USED FOR PART DESIGN</p>	<p>UNLESS OTHERWISE SPECIFIED UNITS ARE: mm [inch]</p>	<p>LATEST VERSION 2/28/2023</p>	<p>SHEET 1 OF 1</p>
------------------	---------------------	--	--	---	-------------------------------------	---------------------