



ISOMETRIC VIEW

AXIAL VERSION

PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, POLYBUTYLENE TEREPHTHALATE HOUSING, THROUGH-BEAM EMITTER, INFRARED LIGHT EMISSION, 25M SENSING DISTANCE, 10-30 VDC OPERATING VOLTAGE, 4-PIN M12 QUICK-DISCONNECT.

F18IE-00-0E

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/28/2023

SHEET 1 OF 1