



PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, POLYBUTYLENE TEREPHTHALATE HOUSING, THROUGH-BEAM RECEIVER, 25M SENSING DISTANCE, 10-30 VDC OPERATING VOLTAGE, SELECTABLE LIGHT-ON/DARK-ON, NPN, 4-PIN M12 QUICK-DISCONNECT.

**F18IR-0N-0E**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
**[inch]**

LATEST VERSION  
2/28/2023

SHEET 1 OF 1