



PROSENSE PHOTOELECTRIC SENSOR, TUBULAR, THREADED, DIFFUSE WITH BACKGROUND SUPPRESSION, 50-150MM SENSING DISTANCE, COMPLEMENTARY LIGHT-ON/DARK-ON, PNP, TEACH-IN BUTTON, 500 HZ SWITCHING FREQUENCY, 4-PIN M12 QUICK-DISCONNECT.

F18RS-BP-0E

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
2/24/2023

SHEET 1 OF 1