



FANDIS VIRDIS SERIES INTAKE FAN, SIDE MOUNT, 9.4 CFM, 24 VDC OPERATING VOLTAGE, G3 (COARSE) FILTER MAT, NEMA 12, INDOOR USE ONLY, 3.62 X 3.62IN ENCLOSURE CUTOUT, ANSI 61 GRAY.

**FF08D24ZN**

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>mm</b> [inch]	LATEST VERSION 3/23/2022	SHEET 1 OF 1
--	-----------	--------------	---	-----------------------------------	---------------------------------------	---------------------	-----------------------------	--------------