



FANDIS VIRDIS SERIES INTAKE FAN, SIDE MOUNT, 29 CFM, 115 VAC OPERATING VOLTAGE, G3 (COARSE) FILTER MAT, NEMA 12, INDOOR USE ONLY, 4.88 X 4.88IN ENCLOSURE CUTOUT, RAL 7035 LIGHT GRAY.

**FF12A115UF**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

**mm**  
[inch]

LATEST VERSION  
3/23/2022

SHEET 1 OF 1