



FANDIS VIRDIS SERIES INTAKE FAN, SIDE MOUNT, 29 CFM, 230 VAC OPERATING VOLTAGE, G3 (COARSE) FILTER MAT, NEMA 12, INDOOR USE ONLY, 4.88 X 4.88IN ENCLOSURE CUTOUT, RAL 7035 LIGHT GRAY.

FF12A230UF

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/23/2022

SHEET 1 OF 1