



FANDIS VIRDIS SERIES INTAKE FAN, SIDE MOUNT, 135 CFM, 24 VDC OPERATING VOLTAGE, G4 (COARSE) FILTER MAT, NEMA 3R, SAFE FOR OUTDOOR USE, 8.78 X 8.78IN ENCLOSURE CUTOUT, RAL 9005 BLACK.

FF15D24NF53

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
3/23/2022

SHEET 1 OF 1