



ProSense FLOAT LIQUID LEVEL SWITCH, HORIZONTAL SIDE MOUNT, 4.43in INSERTION LENGTH, 0.92in DIAMETER FLOAT, BUNA-N, 304 SS, TEFLON, CERAMIC WETTED PARTS, -40 TO 221 DEG F, 1in MALE NPT PROCESS CONNECTION, SPST REED SWITCH, N.O./N.C. SELECTABLE

FLS-HL-400

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
3/24/2022

SHEET 1 OF 1