

72.00 [1829.5]
#22 AWG HALAR
LIQUID TIGHT FITTING
3/4-14 NPT

RETAINING CLIP
Ø 0.90 [22.9] MAX
1.13 [28.6]

31.00±0.125 [787.4±3.2] ACTUATION POINT
1.25 [31.8] MAX
1.00±0.125 [25.4±3.2] ACTUATION POINT
72.00 [1829.5]
32.00±0.125 [812.8±3.2]

ProSense FLOAT LIQUID LEVEL SWITCH, VERTICAL TOP MOUNT, 32in INSERTION LENGTH, 0.9in DIAMETER FLOAT, BUNA-N, BRASS
WETTED PARTS, -40 TO 221 DEG F, 3/4in MALE NPT PIPE PLUG PROCESS CONNECTION, SPST REED SWITCH, (1) N.O. & (1) N.C.

FLS-VD-300

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
3/24/2022

SHEET 1 OF 1