



72.00 [1829.5]
 #22 AWG HALAR
 LIQUID TIGHT FITTING
 3/4-14 NPT



RETAINING CLIP
 Ø0.90 [22.9] MAX
 1.13 [28.6]



ProSense FLOAT LIQUID LEVEL SWITCH, VERTICAL TOP MOUNT, 32in INSERTION LENGTH, 0.9in DIAMETER FLOAT, 316 SS
 WETTED PARTS, -40 TO 302 DEG F, 3/4in MALE NPT PIPE PLUG PROCESS CONNECTION, SPST REED SWITCH, (1) N.O. & (1) N.C.

FLS-VD-600

AutomationDirect.com
 1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 3/24/2022	SHEET 1 OF 1
--	-----------	--------------	---	---------------------------------	---------------------------------------	-----------	--------------------------	--------------