



PANEL MOUNT, 20-260 VAC INPUT VOLTAGE, SPST, (1) N.O. SCR, 90A CONTACT RATING, 24-230 VAC LOAD VOLTAGE, SCREW TERMINAL(s), OVERVOLTAGE PROTECTION. THERMAL MOUNTING PAD INCLUDED.

GEFRAN SOLID STATE RELAY

GQ-90-24-A-1-3

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/28/2024

SHEET 1 OF 1